



Ethene, Ethylene Gas Sensor C2H4/S-1500

C2H4 Gas Sensor in Standard Housing

Applications

- · Discontinuous Measurement
- Fruit Ripening

Measurement

Operation Principle	3-Electrode Electrochemical
Nominal Range	0 - 1500 ppm
Maximum Overload	3000 ppm
Inboard Filter	-
Output Signal	12 ± 4 nA/ppm
Resolution (Electronics dependent)	< 4 ppm
T80 Response Time	< 60 s
Typical Baseline Range (pure air, 20°C)	-10 ppm to 35 ppm
Maximum Zero Shift (+20°C to +40°C)	73 ppm
Repeatability	< 2 % of signal
Output Linearity	Linear
Gain (Only applies to 4-Electrode sensors)	-

Rev.: Apr-20 Page 1 of 4

Phone: +41 43 311 72 00 Fax: +41 43 311 72 01 E-Mail: info@membrapor.ch Website: www.membrapor.ch Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland

Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





Ethene, Ethylene Gas Sensor C2H4/S-1500

Electrical

Rec. Load Resistor	10 - 33 Ω
Bias (V_Sens-V_Ref)	not recommended
Conformity to RoHS directive	RoHS Compliance

Environmental

Relative Humidity Range	15 % to 90 % RH non-condensing
Temperature Range	-40 °C to 50 °C
Pressure Range	Atmospheric ± 10%
Pressure Coefficient	N.D.
Humidity Effect	None

Lifetime

Expected Operation Life	2 years in air
Expected Long Term Output Drift in air	< 5 % signal loss per month
Filter Life	
Storage Life	6 months in container
Rec. Storage Temperature	5°C - 20°C
Warranty Period	12 months from date of dispatch

Rev.: Apr-20 Page 2 of 4

Phone: +41 43 311 72 00
Fax: +41 43 311 72 01
E-Mail: info@membrapor.ch
Website: www.membrapor.ch

Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland


Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





Ethene, Ethylene Gas Sensor C2H4/S-1500

Standard-Size Outline Dimensions



Mechanical

Weight 32 g

Orientation Any

Housing material Polycarbonate

Rev.: Apr-20 Page 3 of 4

Phone: +41 43 311 72 00

Fax: +41 43 311 72 01

E-Mail: info@membrapor.ch

Website: www.membrapor.ch

Website: www.membrapor.ch

Switzerland

Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar





Ethene, Ethylene Gas Sensor C2H4/S-1500

Cross Sensitivity Data

The table below does not claim to be complete. Interfering gases should not be used for calibration. Please contact Membrapor AG for further support regarding cross sensitivities.

Interfering Gas Cross-Sens. [%]

CO < 60

Rev.: Apr-20 Page 4 of 4

Phone: +41 43 311 72 00 Fax: +41 43 311 72 01 E-Mail: info@membrapor.ch Website: www.membrapor.ch Membrapor AG Birkenweg 2 CH-8304 Wallisellen Switzerland

Performance data recorded at 20 - 25 °C, 30 - 50% RH, 900 - 1100 mbar